



PrimaVision Mini for CDM

HID-PV m 35/I CDM 220-240V 50/60Hz

Miniature HID electronic gear for PGJ5 CDM lamps – freeing up the boundaries of creativity and innovation in luminaire design

Product data


Operating and Electrical			
Input Voltage	220 to 240 V		
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		
Earth Leakage Current (Max)	0.5 mA		
Inrush Current Width	0.25 ms		
Inrush Current Peak (Max)	15 A		
Number of Products on MCB (16A Type B)	24		
(Nom)			
Wiring			
Cable Length From Device to Lamp	2 m		
Connector Type	Insert		
Temperature			
Ambient temperature range	-20 °C to 45 °C		
T-Case Lifetime (Nom)	85 °C		
T-Case Maximum (Max)	85 ℃		

Mechanical and Housing				
Housing	Independent			
Approval and Application				
Approval Marks	F-Marking CE marking ENEC certificate CB			
	Certificate			
Product Data				
Order product name	HID-PV m 35/I CDM 220-240V 50/60Hz			
Full product name	HID-PV m 35/I CDM 220-240V 50/60Hz			
Full product code	872790089164500			
Order code	913700653566			
Material Nr. (12NC)	913700653566			
Numerator - Quantity Per Pack	1			
EAN/UPC - Product/Case	8711500881724			
Numerator - Packs per outer box	10			
EAN/UPC - Case	8727900891645			

Datasheet, 2024, March 21 data subject to change

PrimaVision Mini for CDM

Dimensional drawing



Product	D1	C1	A1	A2	А3	B1
HID-PV m 35/I CDM	4.8 mm	34.0 mm	234.7 mm	225.1 mm	202.0 mm	49.4 mm
220-240V 50/60Hz						

