

HID ignitors for MK4 semi-parallel systems

SKD 578 220-240V 50/60Hz

HID ignitors for semi-parallel systems


Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Wiring	
Connector Type	Screw
Temperature	
Ambient temperature range	-30 °C to 85 °C
T-Case Maximum (Max)	90 °C
Approval and Application	
Approval Marks	CE marking ENEC certificate

Product Data	
Order product name	SKD 578 220-240V 50/60Hz
Full product name	SKD 578 220-240V 50/60Hz
Full product code	872790089567400
Order code	89567400
Material Nr. (12NC)	913700655366
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900771312
Numerator - Packs per outer box	48
EAN/UPC - Case	8727900895674

HID ignitors for MK4 semi-parallel systems

Dimensional drawing



Product	A1	B1	C1
SKD 578 220-240V 50/60Hz	63.5 mm	40.5 mm	28 mm

Product
SKD 578 220-240V 50/60Hz

