


HID ignitors for MK4 semi-parallel systems

SKD 578 220-240V 50/60Hz

HID ignitors for semi-parallel systems

Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz

Wiring	
Connector Type	Screw


Temperature	
Ambient temperature range	-30 °C to 85 °C
T-Case Maximum (Max)	90 °C

Approval and Application	
Approval Marks	CE marking ENEC certificate

Product Data	
Order product name	SKD 578 220-240V 50/60Hz
Full product name	SKD 578 220-240V 50/60Hz
Full product code	872790089567400
Order code	913700655366
Material Nr. (12NC)	913700655366
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900771312
Numerator - Packs per outer box	48
EAN/UPC - Case	8727900895674

HID ignitors for MK4 semi-parallel systems

Dimensional drawing



Product	A1	B1	C1
SKD 578 220-240V 50/60Hz	63.5 mm	40.5 mm	28 mm

Product
SKD 578 220-240V 50/60Hz

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.