



HID ignitors for MK4 semi-parallel systems

SKD 578-S 220-240V 50/60Hz

HID ignitors for semi-parallel systems

Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz

Wiring	
Connector type	Screw


Temperature	
Ambient temperature range	-30°C to 85°C
T-Case maximum (max.)	90 °C

Approval and Application	
Approval marks	CE marking ENEC certificate

Product Data	
Order product name	SKD 578-S 220-240V 50/60Hz
Full product name	SKD 578-S 220-240V 50/60Hz
Full EOC	872790089569800
Order code	89569800
Material no. (12 NC)	913700655466
Local order code	SKD 578S
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500881779
Numerator – packs per outer box	20
EAN/UPC - Case	8727900895698

HID ignitors for MK4 semi-parallel systems

Dimensional drawing



Product	A1	B1	C1
SKD 578-S 220-240V 50/60Hz	67.5 mm	40.5 mm	28.0 mm

