



# PrimaVision Mini for CDM

## HID-PV m PGJ5 20/S CDM HPF 220-240V


Miniature HID electronic gear for PGJ5 CDM lamps – freeing up the boundaries of creativity and innovation in luminaire design

### Product data

Operating and Electrical		Mechanical and Housing	
Input Voltage	220 to 240 V	Housing	Standard
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz	Approval and Application	
Earth Leakage Current (Max)	0.25 mA	Approval Marks	F-Marking CE marking ENEC certificate CB Certificate
Inrush Current Width	0.40 ms		
Inrush Current Peak (Max)	15 A	Product Data	
Number of Products on MCB (16A Type B) (Nom)	24	Order product name	HID-PV m PGJ5 20/S CDM HPF 220-240V
		Full product name	HID-PV m PGJ5 20/S CDM HPF 220-240V
		Full product code	872790077128200
		Order code	913700656766
		Material Nr. (12NC)	913700656766
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8711500881885
		Numerator - Packs per outer box	12
		EAN/UPC - Case	8727900771282
Wiring			
Cable Length From Device to Lamp	2 m		
Connector Type	Insert		
Temperature			
Ambient temperature range	-20 °C to 50 °C		
T-Case Lifetime (Nom)	85 °C		
T-Case Maximum (Max)	85 °C		

# PrimaVision Mini for CDM

## Dimensional drawing



Product	D1	C1	A1	A2	B1
HID-PV m PGJ5 20/S CDM HPF 220-240V	4.2 mm	30.0 mm	97.3 mm	88.3 mm	43.3 mm

