



# HID-GreenVision GP-SON

## HID-GV800 1000W/P GP-SON 400V

Full electronic driver for GP-SON 600/1000W lamps

### Product data


Operating and Electrical	
Input Voltage	400 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Inrush Current Width	1.6 ms
Inrush Current Peak (Max)	30 A
Wiring	
Connector Type	JST VH Connector
Temperature	
Ambient temperature range	0 °C to 35 °C
T-Case Lifetime (Nom)	70 °C
Controls and Dimming	
Control Interface	DIM
Mechanical and Housing	
Housing	L 181x150x58

Approval and Application	
Energy Efficiency Index	A2
Surge Protection (Common/Differential)	EN61547 (L-L 2kV, L-G 4kV) kV
Safety Standard	EN60928, 60926
Environmental Standard	ISO 14001
Approval Marks	CE marking ENEC certificate CB Certificate KEMA Keur certificate

Product Data	
Order product name	HID-GV800 1000W/P GP-SON 400V
Full product name	HID-GV800 1000W/P GP-SON 400V
Full product code	872790090906700
Order code	913700660461
Material Nr. (12NC)	913700660461
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500999528
Numerator - Packs per outer box	144
EAN/UPC - Case	8727900909067

# HID-GreenVision GP-SON

## Dimensional drawing



Product	C1	A1	B1
HID-GVIII 1000W/P GP-SON 400V	58 mm	181 mm	150 mm

