



# **AspiraVision Compact** for CDM

# HID-AV C 35-70 /C CDM 220-240V 50/60Hz

AspiraVision is the mark of excellence in HID electronic gear technology — high-end, compact, lightweight and easy to use, with added features for optimal performance of 35, 50 and 70 W CDM lamps. The recently added switching function provides maximum flexibility for users by integrating three different wattage choices into a single driver.

### **Product data**

Operating and Electrical				
Input Voltage	220 to 240 V			
Line Frequency	50 to 60 Hz			
Input frequency	50 to 60 Hz			
Earth leakage current (max.)	250 mA			
Inrush current width	10 ms			
Inrush current peak (max.)	8 A			
Number of products on MCB (16 A type	58			
B) (nom.)				
Wiring				
Cable length from device to lamp	2 m			
Connector type	GST 18i3 Male w/o Lock			
Temperature				
Ambient temperature range	-20°C to 45°C			
T-case lifetime (nom.)	80 ℃			

Controls and Dimming				
Control interface	-			
Mechanical and Housing				
Housing	/C			
Approval and Application				
Surge Protection (Common/Differential)	EN61547 (L-L 2 kV, L-G 4 kV) kV			
Safety standard	EN 61347-2-12 and 2-1			
Approval marks	EMC HEE F-Marking CE marking ENEC			
	certificate VDE certificate CB Certificate VDE			
	marking C-Tick certificate China Quality			
	Certificate			
Product Data				
Order product name	HID-AV C 35-70 /C CDM 220-240V 50/60Hz			
Full product name	HID-AV C 35-70 /C CDM 220-240V 50/60Hz			
Full EOC	871829123314500			
Order code	23314500			
Material no. (12 NC)	913700684166			


Datasheet, 2023, April 15 data subject to change

# **AspiraVision Compact for CDM**

Local order code	HIDAVTW3570C	
SAP numerator – quantity per pack	1	
EAN/UPC — Product/Case	8718291233145	
Numerator – packs per outer box	12	

EAN/UPC - Case	8718291233152	
=: iii, 0: 0 case	0,10231233132	

## Dimensional drawing



Product	D1	C1	A1	A2	B1
HID-AV C 35-70 /C CDM 220-240V	4.8 mm	32.4 mm	162.2 mm	143.0 mm	82.9 mm
50/60Hz					

