



PrimaVision Xtreme for CPO

HID-PV Xt 140 CPO Q 208-277V

Highly reliable electronic drivers for CPO lamps; designed to save energy by offering better light efficiency than magnetic drivers and to reduce maintenance costs thanks to 80,000-hour lifetime and integrated lightning protection

Product data

| 208-240-277 V |
|-----------------|
| 50 to 60 Hz |
| 50 to 60 Hz |
| 0.7 mA |
| 0.47 ms |
| 0.75 A |
| 52 A |
| 5 |
| |
| |
| |
| 10 m |
| WAGO series 804 |
| |
| |
| -30 °C to 55 °C |
| 80 °C |
| |
| |


| Mechanical and Housing | | | | | | | |
|--|---|--|--|--|--|--|--|
| Housing | Q | | | | | | |
| | | | | | | | |
| Approval and Application | | | | | | | |
| Surge Protection (Common/Differential) | EN61547 (L-L 2kV, L-G 4kV), 10 kV TIL | | | | | | |
| Safety Standard | IEC 607, 609, 926, 928 [No Standard for HID | | | | | | |
| | Lamp drivers exists. Requirements in these | | | | | | |
| | standards to be used if considered relevant | | | | | | |
| | for the product.] | | | | | | |
| Environmental Standard | ISO 14001 | | | | | | |
| Approval Marks | F-Marking CE marking ENEC certificate VDE- | | | | | | |
| | EMV certificate | | | | | | |
| | | | | | | | |
| Product Data | | | | | | | |
| Order product name | HID-PV Xt 140 CPO Q 208-277V | | | | | | |
| Full product name | HID-PV Xt 140 CPO Q 208-277V | | | | | | |
| Full product code | 871829124147800 | | | | | | |
| Local code description | HIDPVXt140/SCPO | | | | | | |
| Order code | 913700685666 | | | | | | |
| Material Nr. (12NC) | 913700685666 | | | | | | |
| Local order code | HIDPVXT140/SCPO | | | | | | |
| Numerator - Quantity Per Pack | 1 | | | | | | |

Datasheet, 2023, April 16 data subject to change

PrimaVision Xtreme for CPO

| EAN/UPC - Product/Case | 8718291241478 |
|---------------------------------|---------------|
| Numerator - Packs per outer box | 12 |
| EAN/UPC - Case | 8718291241485 |

Dimensional drawing



| Product | D1 | C1 | A1 | A2 | B1 | B2 |
|---------------------|--------|---------|----------|----------|---------|---------|
| HID-PV Xt 140 CPO Q | 4.5 mm | 40.0 mm | 150.0 mm | 133.6 mm | 90.0 mm | 70.0 mm |
| 208-277V | | | | | | |

