

# HID-Basic BSN/BMH semi-parallel for SON/CDO/CDM/MH/ HPI

## BMH 70 K302-A2-ITS 230V 50Hz

Impregnated electromagnetic copper/iron ballasts for use with an external semi parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps


### Product data

Operating and Electrical	
Input Voltage	230 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking ENEC certificate
Product Data	
Order product name	BMH 70 K302-A2-ITS 230V 50Hz

Full product name	BMH 70 K302-A2-ITS 230V 50Hz
Full product code	871869674074300
Order code	74074300
Material Nr. (12NC)	913700751726
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696740743
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696740750

HID-Basic BSN/BMH semi-parallel for SON/CDO/CDM/MH/HPI

Dimensional drawing



Product	A1	A2	B1	C1	D1
BMH 70 K302-A2-ITS 230V 50Hz	118 mm	94 mm	61 mm	52 mm	6.2 mm

