



# HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/ HPI

## BSN 70 K302-A2-ITS 230V 50Hz



Impregnated electromagnetic copper ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

### Product data

Operating and Electrical		Full product name	
Input Voltage	230 V		BSN 70 K302-A2-ITS 230V 50Hz
Line Frequency	50 Hz	Full EOC	871869674082800
Input frequency	50 Hz	Order code	74082800
		Material no. (12 NC)	913700752126
		SAP numerator – quantity per pack	1
		EAN/UPC – Product/Case	8718696740828
		Numerator – packs per outer box	6
		EAN/UPC - Case	8718696740835
Wiring			
Connector type	Screw		
Approval and Application			
Approval marks	CE marking ENEC certificate		
Product Data			
Order product name	BSN 70 K302-A2-ITS 230V 50Hz		

# HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/HPI

## Dimensional drawing



Product	A1	A2	B1	C1	D1
BSN 70 K302-A2-ITS 230V 50Hz	118 mm	94 mm	61 mm	52 mm	6.2 mm

