

# HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/ HPI

## BSN 150 K302-A2-ITS 230V 50Hz



Impregnated electromagnetic copper ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

### Product data

Operating and Electrical		Full product name		BSN 150 K302-A2-ITS 230V 50Hz	
Input Voltage	230 V	Full product code		871869674096500	
Line Frequency	50 Hz	Order code		74096500	
Input Frequency	50 Hz	Material Nr. (12NC)		913700752626	
Wiring		Numerator - Quantity Per Pack		1	
		EAN/UPC - Product/Case		8718696740965	
		Numerator - Packs per outer box		6	
Connector Type	Screw	EAN/UPC - Case		8718696740972	
Approval and Application					
Approval Marks	CE marking ENEC certificate				
Product Data					
Order product name	BSN 150 K302-A2-ITS 230V 50Hz				

HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/HPI

Dimensional drawing



Product	A1	A2	B1	C1	D1
BSN 150 K302-A2-ITS 230V 50Hz	134 mm	113 mm	76 mm	65 mm	6.2 mm

