


HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

BSN 150 L33-A2-TS 230V 50Hz

Encapsulated electromagnetic copper/iron ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps (no ignitor needed for SON-I lamps)

Product data

Operating and Electrical	
Input Voltage	230 V
Line Frequency	50 Hz
Input Frequency	50 Hz

Wiring	
Connector Type	Screw


Approval and Application	
Approval Marks	CE marking ENEC certificate

Product Data	
Order product name	BSN 150 L33-A2-TS 230V 50Hz

Full product name	BSN 150 L33-A2-TS 230V 50Hz
Full product code	871869674100900
Order code	74100900
Material Nr. (12NC)	913700752826
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696741009
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696741016

HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

Dimensional drawing



Product	A1	A2	B1	C1	D1
BSN 150 L33-A2-TS 230V 50Hz	126 mm	108 mm	81 mm	66 mm	6.2 mm

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.