




HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

BSN 150 L33-A2-TS 230V 50Hz


Encapsulated electromagnetic copper/iron ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

Product data

Operating and Electrical		Full product name		BSN 150 L33-A2-TS 230V 50Hz	
Input Voltage	230 V	Full EOC		871869674100900	
Line Frequency	50 Hz	Order code		74100900	
Input frequency	50 Hz	Material no. (12 NC)		913700752826	
		SAP numerator – quantity per pack		1	
		EAN/UPC — Product/Case		8718696741009	
		Numerator – packs per outer box		6	
		EAN/UPC - Case		8718696741016	
Approval and Application					
Approval marks		CE marking ENEC certificate			
Product Data					
Order product name		BSN 150 L33-A2-TS 230V 50Hz			

HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

Dimensional drawing



Product	A1	A2	B1	C1	D1
BSN 150 L33-A2-TS 230V 50Hz	126 mm	108 mm	81 mm	66 mm	6.2 mm

