



# HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/ HPI

## BSN 250 K302-A2-ITS 230V 50Hz

Impregnated electromagnetic copper ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

### Product data

<b>Operating and Electrical</b>		<b>Full product name</b>		BSN 250 K302-A2-ITS 230V 50Hz	
Input Voltage	230 V	<b>Full EOC</b>		871869674102300	
Line Frequency	50 Hz	<b>Order code</b>		74102300	
Input frequency	50 Hz	<b>Material no. (12 NC)</b>		913700752926	
		<b>SAP numerator – quantity per pack</b>		1	
		<b>EAN/UPC — Product/Case</b>		8718696741023	
		<b>Numerator – packs per outer box</b>		6	
		<b>EAN/UPC - Case</b>		8718696741030	
<b>Approval and Application</b>					
Approval marks		CE marking ENEC certificate			
<b>Product Data</b>					
Order product name		BSN 250 K302-A2-ITS 230V 50Hz			

# HID-Basic BSN/BMH MK4 semi-parallel for SON/CDO/CDM/MH/HPI

## Dimensional drawing



Product	A1	A2	B1	C1	D1
BSN 250 K302-A2-ITS 230V 50Hz	160 mm	139 mm	76 mm	65 mm	6.2 mm

