



HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

BSN 250 L33-A2-TS 230V 50Hz

Encapsulated electromagnetic copper/iron ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps (no ignitor needed for SON-I lamps)

Product data

Operating and Electrical	
Input Voltage	230 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Approval Marks	CE marking ENEC certificate
Product Data	
Order product name	BSN 250 L33-A2-TS 230V 50Hz

Full product name	BSN 250 L33-A2-TS 230V 50Hz
Full product code	871869674108500
Order code	74108500
Material Nr. (12NC)	913700753126
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696741085
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696741092

HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

Dimensional drawing



Product	A1	A2	B1	C1	D1
BSN 250 L33-A2-TS 230V 50Hz	151 mm	132 mm	81 mm	66 mm	6.2 mm

