

HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

BSN 250 L33-A2-TS 230V 50Hz



Encapsulated electromagnetic copper/iron ballasts for use with an external semi-parallel ignitor for CDM, CDO, MH, HPI (Plus) and SON lamps

Product data

Operating and Electrical		Full product name	
Input Voltage	230 V	Full product code	BSN 250 L33-A2-TS 230V 50Hz
Line Frequency	50 Hz	Order code	871869674108500
Input Frequency	50 Hz	Material Nr. (12NC)	913700753126
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8718696741085
		Numerator - Packs per outer box	6
		EAN/UPC - Case	8718696741092
Wiring			
Connector Type	Screw		
Approval and Application			
Approval Marks	CE marking ENEC certificate		
Product Data			
Order product name	BSN 250 L33-A2-TS 230V 50Hz		

HID-HeavyDuty BSN semi-parallel for SON/CDO/MH/HPI

Dimensional drawing



Product	A1	A2	B1	C1	D1
BSN 250 L33-A2-TS 230V 50Hz	151 mm	132 mm	81 mm	66 mm	6.2 mm

