



EB-E Electronic ballasts for TL-D lamps (India)

EBE (Slim) 136 TLD 240V

Compact, lightweight, high-frequency electronic ballast for TL-D lamps


Product data

Operating and Electrical	
Input Voltage	240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Wiring	
Connector Type Input Terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]
Connector Type Output Terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]
Temperature	
Ambient temperature range	0 °C to 50 °C
T-Case Maximum (Max)	65 °C
Approval and Application	
Energy Efficiency Index	Not specified

Safety Standard	- [Not specified]
Product Data	
Order product name	EBE (Slim) 136 TLD 240V
Full product name	EBE (Slim) 136 TLD 240V
Full product code	871829111590800
Order code	913702242021
Material Nr. (12NC)	913702242021
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291115908
Numerator - Packs per outer box	10
EAN/UPC - Case	8718291115908

EB-E Electronic ballasts for TL-D lamps (India)

Dimensional drawing



Product	D1	C1	A1	A2	B1
EBE (Slim) 136 TLD 240V	4.0 mm	21.0 mm	265.0 mm	253.3 mm	30.0 mm

