



# EB-T Electronic ballasts for TL-D lamps (India)

## EBT 218 TLD

Compact, lightweight, high-frequency electronic standard ballasts for TL-D 36 W/ TL40 lamps


### Product data

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Wiring	
Connector Type Input Terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]
Connector Type Output Terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]
Temperature	
Ambient temperature range	0 °C to 50 °C
T-Case Maximum (Max)	75 °C
Approval and Application	
Energy Efficiency Index	A3

Safety Standard	IEC 61347-2-3
Approval Marks	CE marking S Mark
Product Data	
Order product name	EBT 218 TLD
Full product name	EBT 218 TLD
Full product code	872790007852700
Order code	913702249112
Material Nr. (12NC)	913702249112
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500997029
Numerator - Packs per outer box	6
EAN/UPC - Case	8727900078527

## EB-T Electronic ballasts for TL-D lamps (India)

### Dimensional drawing



Product	D1	C1	A1	A2	B1
EBT 218 TLD	4.0 mm	30.0 mm	210.0 mm	200.0 mm	40.0 mm

