

HID-Basic Gearbox system for SON (India)

BSN 070 M261

Impregnated electromagnetic ballasts of copper and steel construction for use in combination with an external ignitor for High-Pressure Sodium Vapor (SON) lamps

Warnings and Safety

- Ballasts are only suitable for use with integrated luminaires


Product data

| Operating and Electrical | |
|--------------------------|---------------|
| Input Voltage | 220/240 V |
| Line Frequency | 50 Hz |
| Input Frequency | 50 Hz |
| Wiring | |
| Connector Type | Screw |
| Approval and Application | |
| Energy Efficiency Index | Not specified |
| Approval Marks | CE marking |

| Product Data | |
|---------------------------------|-----------------|
| Order product name | BSN 070 M261 |
| Full product name | BSN 070 M261 |
| Full product code | 871150088440400 |
| Order code | 913702251012 |
| Material Nr. (12NC) | 913702251012 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500884404 |
| Numerator - Packs per outer box | 12 |
| EAN/UPC - Case | 8727900067378 |

HID-Basic Gearbox system for SON (India)

Dimensional drawing



| Product | D1 | C1 | A1 | A2 | B1 |
|--------------|--------|---------|----------|---------|---------|
| BSN 070 M261 | 6.3 mm | 51.0 mm | 117.0 mm | 98.0 mm | 60.0 mm |

