

HID-Basic BHL for HPL/HPI (India)

BHL 125 M261

Impregnated electromagnetic ballasts of copper and steel construction for High-Pressure Mercury Vapor (HPL) lamps


Product data

Operating and Electrical	
Input Voltage	220/240 V
Line Frequency	50 Hz
Input Frequency	50 Hz
Wiring	
Connector Type	Screw
Approval and Application	
Energy Efficiency Index	Not specified
Product Data	
Order product name	BHL 125 M261

Full product name	BHL 125 M261
Full product code	871150088443500
Order code	913702251612
Material Nr. (12NC)	913702251612
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500884435
Numerator - Packs per outer box	12
EAN/UPC - Case	8727900067415

HID-Basic BHL for HPL/HPI (India)

Dimensional drawing



Product	D1	C1	A1	A2	B1
BHL 125 M261	6.3 mm	51.0 mm	117.0 mm	98.0 mm	60.0 mm

