

HID-Basic Gearbox system for SON (India)

BSN 250 M361

Impregnated electromagnetic ballasts of copper and steel construction for use in combination with an external ignitor for High-Pressure Sodium Vapor (SON) lamps

Warnings and Safety


- Ballasts are only suitable for use with integrated luminaires

Product data

Operating and Electrical		Full product name		BSN 250 M361
Input Voltage	220/240 V	Full product code		871150088467100
Line Frequency	50 Hz	Order code		913702253722
Input Frequency	50 Hz	Material Nr. (12NC)		913702253722
		Numerator - Quantity Per Pack		1
		EAN/UPC - Product/Case		8711500884671
		Numerator - Packs per outer box		4
		EAN/UPC - Case		8727900067675
Approval and Application				
Energy Efficiency Index	Not specified			
Product Data				
Order product name	BSN 250 M361			

HID-Basic Gearbox system for SON (India)

Dimensional drawing



Product	D1	C1	A1	B1	B2
BSN 250 M361	6.3 mm	64.0 mm	143.5 mm	77.5 mm	66.0 mm

