

# Electronic Ignitors for HID lamp circuits (India)

## SN57

Electronic ignitors for HID lamps


### Product data

| Operating and Electrical  |                 |
|---------------------------|-----------------|
| Input Voltage             | 220/240 V       |
| Line Frequency            | 50 to 60 Hz     |
| Input Frequency           | 50 to 60 Hz     |
| Temperature               |                 |
| Ambient temperature range | -20 °C to 90 °C |
| T-Case Maximum (Max)      | 80 °C           |
| Product Data              |                 |
| Full product code         | 871150099636700 |

|                                 |               |
|---------------------------------|---------------|
| Order product name              | SN57          |
| Order code                      | 913702261112  |
| Numerator - Quantity Per Pack   | 1             |
| Numerator - Packs per outer box | 50            |
| Material Nr. (12NC)             | 913702261112  |
| Full product name               | SN57          |
| EAN/UPC - Case                  | 8727900068405 |
| EAN/UPC - Product/Case          | 8711500996367 |

Electronic Ignitors for HID lamp circuits (India)

Dimensional drawing



| Product | D1     | C1      | A1      |
|---------|--------|---------|---------|
| SN57    | 4.3 mm | 37.5 mm | 76.0 mm |

