



Electronic Ignitors for HID lamp circuits (India)

SI51

Electronic ignitors for HID lamps


Product data

| Operating and Electrical | |
|---------------------------|-----------------|
| Input Voltage | 220/240 V |
| Line Frequency | 50 to 60 Hz |
| Input Frequency | 50 to 60 Hz |
| Temperature | |
| Ambient temperature range | -20 °C to 80 °C |
| T-Case Maximum (Max) | 90 °C |
| Product Data | |
| Order product name | SI51 |

| | |
|---------------------------------|-----------------|
| Full product name | SI51 |
| Full product code | 871150088411400 |
| Order code | 913702261212 |
| Material Nr. (12NC) | 913702261212 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500884114 |
| Numerator - Packs per outer box | 50 |
| EAN/UPC - Case | 8727900066944 |

Electronic Ignitors for HID lamp circuits (India)

Dimensional drawing



| Product | D1 | C1 | A1 |
|---------|--------|---------|---------|
| SI51 | 4.3 mm | 37.5 mm | 76.0 mm |

