



# Dynalite Leading Edge Dimmers

## DLE410

4 channel Leading Edge Dimmer Controller with a maximum load per channel of 10 A.


The Philips Dynalite DLE410 is a four channel leading edge dimmer controller, with a maximum load per channel of 10 A. - It is suitable for use with incandescent, neon and selected fluorescent light sources, as well as iron core and leading edge electronic transformers. - Ideal for applications where multiple user settings are required  
Interference suppression  
Naturally ventilated  
Soft start and voltage regulation technologies  
Diagnostic functionality  
User controls  
Options available

### Product data


General Information		Order product name	DLE410
CE mark	CE mark	EAN/UPC - Product	8710163505268
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options	Order code	913703006009
EU RoHS compliant	Yes	Numerator - Quantity Per Pack	1
		Numerator - Packs per outer box	1
		Material Nr. (12NC)	913703006009
		Net Weight (Piece)	8.450 kg
Application Conditions			
Ambient temperature range	0 to +40 °C		
Product Data			
Full product code	871016350526800		

# Dynalite Leading Edge Dimmers

## Dimensional drawing



Dynalite Leading Edge Dimmers



Dynalite Leading Edge Dimmers

