



Variateurs à coupure de phase Dynalite

DLE1203

12 channel Leading Edge Dimmer Controller with a maximum load per channel of 3 A.


The Philips Dynalite DLE1203 is a 12 channel leading edge dimmer controller, with a maximum load of 3 A per channel and a total device load of 32 A. - It is suitable for use with incandescent, neon and selected fluorescent lighting, as well as iron core and leading edge electronic transformers. - Interference suppression Naturally ventilated Soft start and voltage regulation technologies Diagnostic functionality Options available

Données du produit


Caractéristiques générales		Désignation Produit	DLE1203
Marquage CE	Marquage CE	Code barre produit (EAN)	8710163505367
Remarques	Please download the Lighting - Product Data Sheet for more information and ordering options	Code de commande	50536700
Conforme à la directive RoHS UE	Oui	Local Code	DLE1203
Conditions d'utilisation		Unité d'emballage	1
Plage de températures ambiantes	0 à +40 °C	Conditionnement par carton	1
Données logistiques		Code industriel (12NC)	913703008009
Code de produit complet	871016350536700	Poids net (pièce)	5,650 kg

Variateurs à coupure de phase Dynalite

Schéma dimensionnel



Dynalite Leading Edge Dimmers



Dynalite Leading Edge Dimmers

