



Dynalite Leading Edge Dimmers

DLE1205

12 channel Leading Edge Dimmer Controller with a maximum load per channel of 5 A.

The Philips Dynalite DLE1205 is a 12 channel leading edge dimmer controller with a maximum load per channel of 5 A. – It is suitable for use with incandescent and neon light sources, as well as iron core and leading edge electronic transformers. – Fully rated deviceInterference suppressionNaturally ventilatedSoft start and voltage regulation technologiesDiagnostic functionalityUser controlsOptions available


产品数据

基本資訊	
CE 標誌	CE
備註	Please download the Lighting – Product Data Sheet for more information and ordering options
符合歐盟 RoHS 標準	是
適用條件	
環境溫度範圍	0 to +40 °C
產品參數	
完整產品碼	871016350542800


訂購產品名稱	DLE1205
EAN/UPC - 產品	8710163505428
訂購代碼	913703010009
分子 - 各件數量	1
分子 - 每一外盒內件數	1
材質 Nr. (12NC)	913703010009
淨重 (件)	13.200 kg

Dynalite Leading Edge Dimmers

二维绘图



DLE1205



DLE1205

