



Dynalite Leading Edge Dimmers

DLE1205

12 channel Leading Edge Dimmer Controller with a maximum load per channel of 5 A.


The Philips Dynalite DLE1205 is a 12 channel leading edge dimmer controller with a maximum load per channel of 5 A. - It is suitable for use with incandescent and neon light sources, as well as iron core and leading edge electronic transformers. - Fully rated device
Interference suppression
Naturally ventilated
Soft start and voltage regulation technologies
Diagnostic functionality
User controls
Options available

Dados do produto


Informações gerais		Nome de produto da encomenda	
Marca CE	CE	Nome de produto da encomenda	DLE1205
Observações	Please download the Lighting - Product Data Sheet for more information and ordering options	EAN/UPC - Produto	8710163505428
Marca RoHS	RoHS mark	Código de encomenda	913703010009
Condições de aplicação		Código de encomenda local	913703010009
Intervalo de temperatura ambiente	0 to +40 °C	Numerador SAP - Quantidade por embalagem	1
Dados do produto		Numerador SAP - Embalagens por exterior	1
Código do produto completo	871016350542800	Nº do material (12NC)	913703010009
		Peso líquido SAP (peça)	13,200 kg

Dynalite Leading Edge Dimmers

Desenho dimensional



Dynalite Leading Edge Dimmers



Dynalite Leading Edge Dimmers

