



Variateurs à coupure de phase Dynalite

DLE1220GL

12 channel Leading Edge Dimmer Controller with a maximum load per channel of 20 A.

The Philips Dynalite DLE1220GL is a 12 channel leading edge dimmer controller, with a maximum load per channel of 20 A and total device load of 180 A. - It is suitable for use with incandescent, neon and selected fluorescent light sources, as well as iron core and leading edge dimmable electronic transformers. - Large load capability DMX512 compatibility Interference suppression Naturally ventilated Soft start and voltage regulation technologies Diagnostic functionality User controls Options available


Données du produit

Caractéristiques générales	
Marquage CE	Marquage CE
Remarques	Please download the Lighting - Product Data Sheet for more information and ordering options
Conforme à la directive RoHS UE	Oui
Conditions d'utilisation	
Plage de températures ambiantes	0 à +40 °C
Données logistiques	
Code de produit complet	871016350572500


Désignation Produit	DLE1220GL
Code barre produit (EAN)	8710163505725
Code de commande	50572500
Local Code	DLE1220GL-S
Unité d'emballage	1
Conditionnement par carton	1
Code industriel (12NC)	913703016009
Poids net (pièce)	29,000 kg

Variateurs à coupure de phase Dynalite

Schéma dimensionnel



Dynalite Leading Edge Dimmers



Dynalite Leading Edge Dimmers

