



# Dynalite Leading Edge Dimmers

## DLE1220GL

12 channel Leading Edge Dimmer Controller with a maximum load per channel of 20 A.

The Philips Dynalite DLE1220GL is a 12 channel leading edge dimmer controller, with a maximum load per channel of 20 A and total device load of 180 A. - It is suitable for use with incandescent, neon and selected fluorescent light sources, as well as iron core and leading edge dimmable electronic transformers. - Large load capability DMX512 compatibility Interference suppression Naturally ventilated Soft start and voltage regulation technologies Diagnostic functionality User controls Options available


### Dados do produto

Informações gerais	
Marca CE	CE
Observações	Please download the Lighting - Product Data Sheet for more information and ordering options
Compatível com EU RoHS	Sim
Condições de aplicação	
Intervalo de temperatura ambiente	0 to +40 °C
Dados do produto	
Código do produto completo	871016350572500


Nome de produto da encomenda	DLE1220GL
EAN/UPC - Produto	8710163505725
Código de encomenda	913703016009
Código de encomenda local	913703016009
Numerador SAP - Quantidade por embalagem	1
Numerador SAP - Embalagens por exterior	1
Nº do material (12NC)	913703016009
Peso líquido SAP (peça)	29.000 kg

# Dynalite Leading Edge Dimmers

## Desenho dimensional



Dynalite Leading Edge Dimmers



Dynalite Leading Edge Dimmers

