



# Variateurs à coupure de phase Dynalite

## DTE1210

12 channel Trailing Edge Dimmer Controller with a maximum load per channel of 10 A.

The Philips Dynalite DTE1210 trailing edge dimmer controller features 12 channels, with a maximum load per channel of 10 A and a total box load of 120 A. - The trailing edge output makes the device suitable for control of both trailing and leading edge electronic transformers, as well as incandescent lamps and track lighting. - Operates from three phase supply Voltage regulation and soft start technologies Naturally ventilated Interface to other devices Internal controls Options available

### Données du produit

Caractéristiques générales	
Marquage CE	Marquage CE
Remarques	Please download the Lighting - Product Data Sheet for more information and ordering options
Conforme à la directive RoHS UE	Oui

Conditions d'utilisation	
Plage de températures ambiantes	0 à +40 °C


Données logistiques	
Code de produit complet	871016350586200


Désignation Produit	DTE1210
Code barre produit (EAN)	8710163505862
Code de commande	50586200
Local Code	DTE1210
Unité d'emballage	1
Conditionnement par carton	1
Code industriel (12NC)	913703022009
Poids net (pièce)	16,000 kg

# Variateurs à coupure de phase Dynalite

## Schéma dimensionnel



Dynalite Trailing Edge Dimmers



Dynalite Trailing Edge Dimmers

