



Dynalite Multipurpose Controllers

DMC810GL

Within any project, many different lighting load types may be required to achieve a desired result. Each of these load types may require a different style of control. The Philips Dynalite range of multipurpose controllers allows customization of output types via different output module units. When using DIN-rail multipurpose controllers, a specific type of control can be chosen for each circuit: relay, leading-edge dimmer, trailing-edge dimmer, ballast control, controller with out-of-the-box functionality, fan control, and blind/screen control. In any combination, multiple load types can be controlled from a single device. This simplifies installation and prevents wasted capacity of circuits that are not required.

Product data

General Information			
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options	Full product name	DMC810GL
CE mark	CE mark	Full product code	871016350632600
EU RoHS compliant	Yes	Order code	50632600
Temperature		Material Nr. (12NC)	913703028009
Ambient temperature range	0 to +40 °C	Numerator - Quantity Per Pack	1
Product Data		EAN/UPC - Product/Case	8710163506326
Order product name	DMC810GL	Numerator - Packs per outer box	1
		EAN/UPC - Case	8710163506333

Dynalite Multipurpose Controllers

Dimensional drawing

