



Dynalite Signal Dimmer Controllers

DMBC110

The Dynalite range of Signal Dimmer Controllers, have been engineered to meet the future demands of projects. They are capable of transmitting all industry standard driver protocols (1-10V, DSI, DALI and Broadcast DALI) and support two ranges of install opportunities of both DIN-rail and wall box, to allow for flexible install opportunities. The Signal Dimmer Controller range also support a vast range of driver controllers with a variety of circuit numbers and sizes to work individually or as part of a system, suiting any project requirement.

Product data

General Information			
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options	Full product name	DMBC110
CE mark	CE mark	Full product code	871016350636400
EU RoHS compliant	Yes	Order code	913703030009
		Material Nr. (12NC)	913703030009
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8710163506364
		Numerator - Packs per outer box	1
		EAN/UPC - Case	8710163506371
Temperature			
Ambient temperature range	0 to +50 °C		
Product Data			
Order product name	DMBC110		

Dynalite Signal Dimmer Controllers

Dimensional drawing

