



Dynalite Signal Dimmer Controllers

DDBC300-D

The Dynalite range of Signal Dimmer Controllers, have been engineered to meet the future demands of projects. They are capable of transmitting all industry standard driver protocols (1-10V, DSI, DALI and Broadcast DALI) and support two ranges of install opportunities of both DIN-rail and wall box, to allow for flexible install opportunities. The Signal Dimmer Controller range also support a vast range of driver controllers with a variety of circuit numbers and sizes to work individually or as part of a system, suiting any project requirement.

Product data

General Information		Full product name		DDBC300-D
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options	Full product code	871016350641800	
CE mark	CE mark	Order code	913703031109	
EU RoHS compliant	Yes	Material Nr. (12NC)	913703031109	
Temperature		Numerator - Quantity Per Pack	1	
Ambient temperature range	0 to +40 °C	EAN/UPC - Product/Case	8710163506401	
Product Data		Numerator - Packs per outer box	1	
Order product name	DDBC300-D	EAN/UPC - Case	8710163506418	

Dynalite Signal Dimmer Controllers

Dimensional drawing

