



Dynalite Signal Dimmer Controllers

DDBC320-DALI

The Dynalite range of Signal Dimmer Controllers, have been engineered to meet the future demands of projects. They are capable of transmitting all industry standard driver protocols (1-10V, DSI, DALI and Broadcast DALI) and support two ranges of install opportunities of both DIN-rail and wall box, to allow for flexible install opportunities. The Signal Dimmer Controller range also support a vast range of driver controllers with a variety of circuit numbers and sizes to work individually or as part of a system, suiting any project requirement.

Product data

General Information	
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options
CE mark	CE mark
EU RoHS compliant	Yes

Temperature	
Ambient temperature range	0 to +40 °C

Product Data	
Order product name	DDBC320-D

Full product name	DDBC320-DALI
Full product code	871016350642500
Order code	50642500
Material Nr. (12NC)	913703031209
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163506425
Numerator - Packs per outer box	1
EAN/UPC - Case	8710163506432

Dynalite Signal Dimmer Controllers

Dimensional drawing

