



Dynalite Signal Dimmer Controllers

DBC1210

The Dynalite range of Signal Dimmer Controllers, have been engineered to meet the future demands of projects. They are capable of transmitting all industry standard driver protocols (1-10V, DSI, DALI and Broadcast DALI) and support two ranges of install opportunities of both DIN-rail and wall box, to allow for flexible install opportunities. The Signal Dimmer Controller range also support a vast range of driver controllers with a variety of circuit numbers and sizes to work individually or as part of a system, suiting any project requirement.

Product data

General Information	
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options
CE mark	CE mark
EU RoHS compliant	Yes
Temperature	
Ambient temperature range	0 to +50 °C
Product Data	
Order product name	DBC1210

Full product name	DBC1210
Full product code	871016350660900
Order code	913703036009
Material Nr. (12NC)	913703036009
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163506609
Numerator - Packs per outer box	1
EAN/UPC - Case	8710163506616

Dynalite Signal Dimmer Controllers

Dimensional drawing

