



Dynalite Signal Dimmer Controllers

DBC1210

The Dynalite range of Signal Dimmer Controllers, have been engineered to meet the future demands of projects. They are capable of transmitting all industry standard driver protocols (1-10V, DSI, DALI and Broadcast DALI) and support two ranges of install opportunities of both DIN-rail and wall box, to allow for flexible install opportunities. The Signal Dimmer Controller range also support a vast range of driver controllers with a variety of circuit numbers and sizes to work individually or as part of a system, suiting any project requirement.

Product data

General Information			
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options	Full product name	DBC1210
CE mark	CE mark	Full product code	871016350660900
EU RoHS compliant	Yes	Order code	913703036009
Temperature		Material Nr. (12NC)	913703036009
Ambient temperature range	0 to +50 °C	Numerator - Quantity Per Pack	1
Product Data		EAN/UPC - Product/Case	8710163506609
Order product name	DBC1210	Numerator - Packs per outer box	1
		EAN/UPC - Case	8710163506616

Dynalite Signal Dimmer Controllers

Dimensional drawing

