



Dynalite Signal Dimmer Controllers

DBC1220GL

The Dynalite range of Signal Dimmer Controllers, have been engineered to meet the future demands of projects. They are capable of transmitting all industry standard driver protocols (1-10V, DSI, DALI and Broadcast DALI) and support two ranges of install opportunities of both DIN-rail and wall box, to allow for flexible install opportunities. The Signal Dimmer Controller range also support a vast range of driver controllers with a variety of circuit numbers and sizes to work individually or as part of a system, suiting any project requirement.

Product data

General Information			
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options	Full product name	DBC1220GL
CE mark	CE mark	Full product code	871016350668500
EU RoHS compliant	Yes	Order code	913703038009
Temperature		Material Nr. (12NC)	913703038009
Ambient temperature range	0 to +50 °C	Numerator - Quantity Per Pack	1
Product Data		EAN/UPC - Product/Case	8710163506685
Order product name	DBC1220GL	Numerator - Packs per outer box	1
		EAN/UPC - Case	8710163506692

Dynalite Signal Dimmer Controllers

Dimensional drawing

