

Dynalite Signal Dimmer Controllers

DBC1220GL

The Dynalite range of Signal Dimmer Controllers, have been engineered to meet the future demands of projects. They are capable of transmitting all industry standard driver protocols (1-10V, DSI, DALI and Broadcast DALI) and support two ranges of install opportunities of both DIN-rail and wall box, to allow for flexible install opportunities. The Signal Dimmer Controller range also support a vast range of driver controllers with a variety of circuit numbers and sizes to work individually or as part of a system, suiting any project requirement.

Product data

General Information	
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options
CE mark	CE mark
EU RoHS compliant	Yes


Temperature	
Ambient temperature range	0 to +50 °C


Product Data	
Order product name	DBC1220GL

Full product name	DBC1220GL
Full product code	871016350668500
Order code	913703038009
Material Nr. (12NC)	913703038009
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163506685
Numerator - Packs per outer box	1
EAN/UPC - Case	8710163506692

Dynalite Signal Dimmer Controllers

Dimensional drawing





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.