



Dynalite Signal Dimmer Controllers

DBC1220GL

The Dynalite range of Signal Dimmer Controllers, have been engineered to meet the future demands of projects. They are capable of transmitting all industry standard driver protocols (1-10V, DSI, DALI and Broadcast DALI) and support two ranges of install opportunities of both DIN-rail and wall box, to allow for flexible install opportunities. The Signal Dimmer Controller range also support a vast range of driver controllers with a variety of circuit numbers and sizes to work individually or as part of a system, suiting any project requirement.

Product data

General Information		Full product name	
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options	Full product code	871016350668500
CE mark	CE mark	Order code	913703038009
EU RoHS compliant	Yes	Material Nr. (12NC)	913703038009
Temperature		Numerator - Quantity Per Pack	1
Ambient temperature range	0 to +50 °C	EAN/UPC - Product/Case	8710163506685
Product Data		Numerator - Packs per outer box	1
Order product name	DBC1220GL	EAN/UPC - Case	8710163506692

Dynalite Signal Dimmer Controllers

Dimensional drawing

