PHILIPS Lighting



Dynalite LED PWM Controllers

DMX/Dynet via converter interface,

Capable of directly driving LED fittings, the Dynalite LED Dimmers use Pulse Width Modulation (PWM) technology to great effect. Perfectly suited to Red, Green, Blue (RGB) color changing applications, chase sequencing or provision of elegant scene settings. The Dynalite LED drivers come in a range of configurations to meet the compatibility requirements of many of the available LED fittings. Each device is ready to receive native DMX allowing them to be used in color mixing or chase sequence applications.


Product data

General Information	
Remarks	Please download the Lighting - Product Data Sheet for
	more information and ordering options
CE mark	CE mark
EU RoHS compliant	Yes
Temperature	
Ambient temperature range	+32 to +104 °F
Product Data	
Order product name	DDLEDC605GL
Full product name	DMX/Dynet via converter interface,

Full product code	871016351646200
Local code description	DDLEDC605GL
Order code	-
Material Nr. (12NC)	913703061209
Local order code	
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163516462
Numerator - Packs per outer box 1	
EAN/UPC - Case	8710163516479

Dynalite LED PWM Controllers

Dimensional drawing





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com 2023, April 16 - data subject to change