



Contrôleurs Relais Dynalite

DDRC1220FR-GL-V3

DDRC1220FR-GL provides control of multiple types of switched loads. 12 channel controller supports switched loads - up to 20 A per channel, max. load of 180 A.

DDRC1220FR-GL provides control of multiple types of switched loads. 12 channel controller supports switched loads up to 20 A per channel, max. load of 180 A.

Données du produit

Caractéristiques générales

Remarques	Please download the Lighting - Product Data Sheet for more information and ordering options
-----------	---


Données logistiques

Code de produit complet	871869688795000
Désignation Produit	DDRC1220FR-GL
Code barre produit (EAN)	8718696887950


Code de commande	88795000
Local Code	DDRC1220FRGLV3
Unité d'emballage	1
Conditionnement par carton	1
Code industriel (12NC)	913703243009
Poids net (pièce)	0,900 kg

Contrôleurs Relais Dynalite


Schéma dimensionnel



Dynalite Multipurpose Controllers



Dynalite Multipurpose Controllers



Dynalite Multipurpose Controllers

