PHILIPS Lighting



Dynalite Multipurpose Controllers

DDMC802-V2

Within any project, many different lighting load types may be required to achieve a desired result. Each of these load types may require a different style of control. The Philips Dynalite range of multipurpose controllers allows customization of output types via different output module units. When using DIN-rail multipurpose controllers, a specific type of control can be chosen for each circuit: relay, leading-edge dimmer, trailing-edge dimmer, ballast control, controller with out-of-the-box functionality, fan control, and blind/screen control. In any combination, multiple load types can be controlled from a single device. This simplifies installation and prevents wasted capacity of circuits that are not required.


Product data

General Information	
Remarks	Please download the Lighting – Product Data Sheet
	for more information and ordering options
CE mark	CE mark
EU RoHS compliant	Yes
Temperature	
Ambient temperature range	0 to +40 °C
Product Data	
Order product name	DDMC802

Full product name	DDMC802-V2
Full EOC	871869688800100
Order code	88800100
Material no. (12 NC)	913703243509
SAP numerator - quantity per pack 1	
EAN/UPC - Product/Case	8718696888001
Numerator – packs per outer box	1
EAN/UPC - Case	8718696895009

Dynalite Multipurpose Controllers

Dimensional drawing





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com 2023, April 15 - data subject to change