



# Dynalite Multipurpose Controllers

## DMC-GRMS-UL

Within any project, many different lighting load types may be required to achieve a desired result. Each of these load types may require a different style of control. The Philips Dynalite range of multipurpose controllers allows customization of output types via different output module units. When using DIN-rail multipurpose controllers, a specific type of control can be chosen for each circuit: relay, leading-edge dimmer, trailing-edge dimmer, ballast control, controller with out-of-the-box functionality, fan control, and blind/screen control. In any combination, multiple load types can be controlled from a single device. This simplifies installation and prevents wasted capacity of circuits that are not required.

### Product data

General Information		Full EOC	
Remarks	Please download the Lighting – Product Data Sheet for more information and ordering options	Order code	88765300
		Material no. (12 NC)	913703331209
		SAP numerator – quantity per pack	1
		EAN/UPC – Product/Case	8718696887653
		Numerator – packs per outer box	1
		EAN/UPC – Case	8718696894651
Temperature			
Ambient temperature range	0 to +40 °C		
Product Data			
Order product name	DMC-GRMS-UL		
Full product name	DMC-GRMS-UL		

# Dynalite Multipurpose Controllers

## Dimensional drawing

