



Dynalite Signal Dimmer Controllers

DDBC1200

The Dynalite range of Signal Dimmer Controllers, have been engineered to meet the future demands of projects. They are capable of transmitting all industry standard driver protocols (1-10V, DSI, DALI and Broadcast DALI) and support two ranges of install opportunities of both DIN-rail and wall box, to allow for flexible install opportunities. The Signal Dimmer Controller range also support a vast range of driver controllers with a variety of circuit numbers and sizes to work individually or as part of a system, suiting any project requirement.

Product data

General Information	
CE mark	CE mark
EU RoHS compliant	Yes
Temperature	
Ambient temperature range	0 to +40 °C
Product Data	
Order product name	DDBC1200
Full product name	DDBC1200

Full product code	871869688873500
Order code	88873500
Material Nr. (12NC)	913703333909
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696888735
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696895733