



Dynalite Signal Dimmer Controllers

DDBC1200

The Dynalite range of Signal Dimmer Controllers, have been engineered to meet the future demands of projects. They are capable of transmitting all industry standard driver protocols (1-10V, DSI, DALI and Broadcast DALI) and support two ranges of install opportunities of both DIN-rail and wall box, to allow for flexible install opportunities. The Signal Dimmer Controller range also support a vast range of driver controllers with a variety of circuit numbers and sizes to work individually or as part of a system, suiting any project requirement.

Product data

General Information		Product Data	
CE mark	CE mark	Full product code	871869688873500
EU RoHS compliant	Yes	Order product name	DDBC1200
Approval and Application		EAN/UPC - Product	8718696888735
UL Recognized	Yes	Order code	913703333909
UL Recognized Canada & US	Yes	Numerator - Quantity Per Pack	1
Application Conditions		Numerator - Packs per outer box	1
Ambient temperature range	0 to +40 °C	Material Nr. (12NC)	913703333909
		Net Weight (Piece)	450.000 g