



# Dynalite Signal Dimmer Controllers

## DDBC1200

The Dynalite range of Signal Dimmer Controllers, have been engineered to meet the future demands of projects. They are capable of transmitting all industry standard driver protocols (1-10V, DSI, DALI and Broadcast DALI) and support two ranges of install opportunities of both DIN-rail and wall box, to allow for flexible install opportunities. The Signal Dimmer Controller range also support a vast range of driver controllers with a variety of circuit numbers and sizes to work individually or as part of a system, suiting any project requirement.

### Product data

<b>General Information</b>		<b>Local code description</b>	
CE mark	CE mark	Order code	DDBC1200
EU RoHS compliant	Yes	Material Nr. (12NC)	913703333909
<b>Temperature</b>		Local order code	913703333909
Ambient temperature range	+32 to +104 °F	Numerator - Quantity Per Pack	1
<b>Product Data</b>		EAN/UPC - Product/Case	8718696888735
Order product name	DDBC1200	Numerator - Packs per outer box	1
Full product name	DDBC1200	EAN/UPC - Case	8718696895733
Full product code	871869688873500		