



# Dynalite Multipurpose Controllers

## DMC2-UL

Multichannel control via two interchangeable modules. The device is available with a variety of control modules to handle various load types and capacities.

Multichannel control via two interchangeable modules. The device is available with a variety of control modules to handle various load types and capacities.


### Product data

General Information	
CE mark	CE mark
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options
Operating and Electrical	
Input frequency	50 to 60 Hz
Input current (nom.)	32A per phase or single phase 63A max A
Approval and Application	
UL Recognized Canada & US	Yes
Application Conditions	
Ambient temperature range	0 to +40 °C

Product Data	
Full product code	871869600701300
Order product name	DMC2-UL
EAN/UPC – product	8718696007013
Order code	913703666009
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	913703666009
Net weight (piece)	7.710 kg

# Dynalite Multipurpose Controllers

## Dimensional drawing



Dynalite Multipurpose Controllers

