



Dynalite Multipurpose Controllers

DMC2-CE

Within any project, many different lighting load types may be required to achieve a desired result. Each of these load types may require a different style of control. The Dynalite range of multipurpose controllers allows customization of output types via different output module units. When using DIN-rail multipurpose controllers, a specific type of control can be chosen for each circuit: relay, leading-edge dimmer, trailing-edge dimmer, driver control, controller with out-of-the-box functionality, fan control, and blind/screen control. In any combination, multiple load types can be controlled from a single device. This simplifies installation and prevents wasted capacity of circuits that are not required.

Product data

General Information	
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options
CE mark	CE mark
EU RoHS compliant	Yes
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Current (Nom)	32A per phase or single phase 63A max A
Temperature	
Ambient temperature range	0 to +40 °C

Product Data	
Order product name	DMC2-CE
Full product name	DMC2-CE
Full product code	871869600702000
Order code	913703666109
Material Nr. (12NC)	913703666109
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696007020
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696014523

Dynalite Multipurpose Controllers

Dimensional drawing

