



Dynalite Multipurpose Controllers

DMC2-CE

Multichannel control via two interchangeable modules. The device is available with a variety of control modules to handle various load types and capacities.

Multichannel control via two interchangeable modules. The device is available with a variety of control modules to handle various load types and capacities.


Product data

General Information	
CE mark	CE mark
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options
EU RoHS compliant	Yes
Operating and Electrical	
Input Frequency	50 to 60 Hz
Input Current (Nom)	32A per phase or single phase 63A max A
Application Conditions	
Ambient temperature range	0 to +40 °C

Product Data	
Full product code	871869600702000
Order product name	DMC2-CE
EAN/UPC - Product	8718696007020
Order code	913703666109
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913703666109
Net Weight (Piece)	7.710 kg

Dynalite Multipurpose Controllers

Dimensional drawing



Dynalite Multipurpose Controllers

