



Dynalite Multipurpose Controllers

DCM-DyNet

Within any project, many different lighting load types may be required to achieve a desired result. Each of these load types may require a different style of control. The Philips Dynalite range of multipurpose controllers allows customization of output types via different output module units. When using DIN-rail multipurpose controllers, a specific type of control can be chosen for each circuit: relay, leading-edge dimmer, trailing-edge dimmer, ballast control, controller with out-of-the-box functionality, fan control, and blind/screen control. In any combination, multiple load types can be controlled from a single device. This simplifies installation and prevents wasted capacity of circuits that are not required.

Product data

General Information	
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options
CE mark	CE mark
EU RoHS compliant	Yes

Temperature	
Ambient temperature range	0 to +40 °C

Product Data	
Order product name	DCM-DyNet

Full product name	DCM-DyNet
Full product code	871869600703700
Order code	913703666209
Material Nr. (12NC)	913703666209
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696007037
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696014530

Dynalite Multipurpose Controllers

Dimensional drawing

